



Aperiodic port is optional

B-B ( 0.16 : 1 )

A ( 0.32 : 1 )

Material: 19mm MDF  
 Finish: To your liking  
 Damping material: Lightly stuffed and evenly distributed - approx. 50g of damping material  
 Optional aperiodic port: 12g of damping material  
 The damping material should be held in place with a metal grid  
 Port may also be placed on the rear of the cabinet

Designed by haavard	Checked by	Approved by	Date	Date 28.06.2012
			A26_cab	
			Edition	Scale